

Panel thermostat

- Small, compact size (17.5 mm wide)
- Snap action thermostatic Bimetal sensor
- Wide temperature setting range
- Long electrical life
- 35 mm rail (EN 60715) mount


NEW 7T.81.0.000.240x




NEW 7T.81.0.000.230x



• Heating control



• Ventilation control



Heating control - Should the panel temperature fall below the (minimum) set temperature the contact will close to call for heat. The contact will open when this set temperature is exceeded.

Ventilation control - Should the panel temperature exceed the (maximum) set temperature then the contact will close to call for cooling. The contact will open when the temperature falls below this set temperature.

For outline drawing see page 2

Contact specification

Contact configuration	1 NC	1 NO
Rated current/Maximum peak current A	10/20	10/20
Rated voltage/ Maximum switching voltage V AC	250/250	250/250
Rated load AC1 VA	2500	2500
Rated load AC15 (230 V AC) VA	250	250
Single phase motor rating AC3 (230 V AC) kW	1.1	1.1
Breaking capacity DC1: 30/110/220 V A	1/0.3/0.15	1/0.3/0.15
Minimum switching load mW (V/mA)	500 (12/10)	500 (12/10)
Standard contact material	AgNi	AgNi

Temperature setting range


Setting range (ventilation)	°C	—	-20...+40	+0...+60
Switch temperature differential	K	—	7 ± 4	
Setting range (heating)	°C	-20...+40	+0...+60	—
Switch temperature differential	K	7 ± 4		—

Technical data

Electrical life at rated load AC1	cycles	100 · 10 ³	100 · 10 ³
Ambient temperature range	°C	-45...+80	-45...+80
Protection category		IP 20	IP 20
Approvals (according to type)			

Ordering information

Example: 7T Series, thermostat for ventilation control, contact activates ventilation should the panel temperature exceed the set value (max+60 °C), 35 mm rail (EN 60715) mount.



Technical data

Insulation

Dielectric strength between open contacts V AC 500

Other data

Screw torque	Nm	0.5	0.5
Max. wire size		solid cable	stranded cable
	mm ²	1 x 2.5	1 x 1.5
	AWG	1 x 12	1 x 16

G

Outline drawings

7T.81
Screw terminal

